



lick





JOB	
AREA	
ITEM NO.	
MODELN	Ю.

MODELS GLYCOL BATH	MODELS REFRIGERATION DECK
GB1	RD060
GB2	RD060-O
GB3	RD120
GB4	RD120-0
GB1-C	RD060-C
GB2-C	

ArcticPOUR Refrigeration Deck

ArcticPOUR Glycol Bath

- INDUSTRY EXCLUSIVE split-deck refrigeration technology features a two-component system of a refrigeration deck and glycol bath.
- Split-deck refrigeration technology provides flexibility in locating the refrigeration deck.
- The refrigeration deck may be located up to 100 feet from the glycol bath. Mounting outdoors removes an indoor heat load of up to 18,000 BTU/Hr.
- ArcticPOUR's glycol bath with optional flash chiller lowers the beer temperature to 6°F below the keg temperature, and can
 produce 32°F beer when the walk-in cooler is 38°F.
- ArcticPOUR can produce beer at two different temperatures, and can accommodate up to three trunk lines to one glycol bath.



Form No. 95172 Rev. 06.13.2017

Sizes and Specifications

Air-Cooled Refrigeration Deck - Drawing on page 3


			Cord Connected					
MODEL NOS.		RD060	RD060-0	RD120	RD120-0	RD060-C		
DIMENSIONS:	Length	31-1/2" (800)	35-15/16" (913)	34-3/8" (873)	38-15/16" (989)	31-1/2" (775)		
EXTERIOR (mm)	Width	17-3/8" (441)	28-1/4" (718)	21-3/4" (552)	33-3/8" (848)	17-3/8″ (445)		
	Height	15-3/16" (386)	15-3/16" (387)	18-1/16" (459)	18-1/16" (459)	15-3/16" (386)		
	A minimum of 12" of clearance should be allowed around the entire unit for proper performance. Additional clearance should be considered for above and in front of the unit for serviceability.							
ELECTRICAL	Voltage	120 V	120 V	208/230 V	208/230 V	120 V		
	Frequency	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz		
	Phase	1 Ø	1 Ø	1 Ø	1 Ø	1 Ø		
	RLA	11.5	11.5	19.3	19.3	11.6		
	МСА	18.4	18.4	23.8	23.8			
	Max Fuse	30.0	30.0	40	40			
	Cord/Plug	N/A	N/A	N/A	N/A	14/3 NEMA 5-15P		
COMPRESSOR		3/4 HP	3/4 HP	1.5 HP	1.5 HP	3/4 HP		
EVAPORATOR RATING @ 20°F (BTUH)		6000	6000	12000	12000	6000		
HEAT REJECTION (MAX)		8100	8100	16800	16800	8100		
REFRIGERANT		R-134a	R-134a	R-134a	R-134a	R-134a		
SHIPPING WEIGHT LBS (kg)		120 (54)	120 (54)	140 (64)	140 (64)	120 (54)		
CABINET		Stainless Steel						
REFRIGERATION		Constant Pressure Expansion Valve, Condensing Unit with Service Valves						
REFRIGERANT CHA	ARGE (grams)	9.5 oz/269 g	9.5 oz/269 g	16 oz/453 g	16 oz/453 g	9.5 oz/269 g		

Glycol Bath - Drawing on page 4

	Permanently Connected				Cord Connected			
MODEL NOS.		GB1	GB2	GB3	GB4	GB1-C	GB2-C	
DIMENSIONS: EXTERIOR (mm)	Length "A"	24-3/4" (629)	24-3/4" (629)	24-3/4" (629)	24-3/4" (629)	24-3/4" (629)	24-3/4" (629)	
	Width "B"	19" (483)	23-11/16" (602)	23-11/16" (602)	23-11/16" (602)	19" (483)	23-11/16" (602)	
	Height "C"	25-5/16" (643)	25-5/16" (643)	25-5/16" (643)	25-5/16" (643)	25-5/16" (643)	25-5/16" (643)	
	A minimum of 6" of clearance should be allowed around the entire unit for proper performance. Additional clearance should be considered for above the unit and in front of the unit for servicability.							
ELECTRICAL	Voltage	120 V	120 V	120 V	120 V	120 V	120 V	
	Frequency	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz	
	Phase	1 Ø	1 Ø	1 Ø	1 Ø	1 Ø	1 Ø	
	RLA	6.5	12.6	18.7	24.8	N/A	N/A	
	МСА	8.7	13.9	19.9	26.2	N/A	N/A	
	Max Fuse	15	20	25	30	N/A	N/A	
	Current/Plug	N/A	N/A	N/A	N/A	5.8, NEMA 5-15	11.6, NEMA 5-15P	
SHIPPING WEIGHT LBS (kg)		140 (64)	140 (64)	140 (64)	140 (64)	140 (64)	140 (64)	
CIRCULATING PUMP #1		140 GPH / 130 PSIG						
CIRCULATING PUMP #2, #3, #4		100 GPH / 130 PSIG						
RESERVOIR CAPACITY		12 gal						
GLYCOL CONCENTRATION		30%	30%	30%	30%	30%	30%	

	67451	Coolant Connector Parts Bag, Refrigeration Deck to Glycol Bath	61790+1	Rack, 37" X 19-3/4", 3-Tiered
IES	67451-1	Coolant Connector, Fabricated, Per Foot, Refrigeration Deck to Glycol Bath		Rack, 37" X 19-3/4", 4-Tiered
	63299-1	Glycol Solution, 1 gallon	57782	Legs, Set of 4, 6" Nom
ACCESSORIES	63335	Coolant Connector Kit (Glycol Bath to Trunk Housing)	68470-1	Wall Shelf, Large (RD120)
CCES	63335-1	Coolant Connector Kit (Glycol Bath to Trunk Housing)	68470-2	Wall Shelf, Small (RD060 or GB)
AC	68455	Flashchill Connector Kit	68508	Rack, ArcticPOUR, Two Tier
	C21499BSS	Stand, 35" X 22"	68508+1	Rack, ArcticPOUR, +1 Extension
	61790	Rack, 37" X 19-3/4", 2-Tiered	68508+2	Rack, ArcticPOUR, +2 Extension

Refrigeration Deck Drawings




PERLICK CORPORATION 8300 W. Good Hope Rd., Milwaukee, WI 53223 • (800) 558-5592 • perlick.com



ARCTICPOUR ADVANCED REFRIGERATION TECHNOLOGY

Glycol Bath Drawings



Form No. 95172 Rev. 06.13.2017